

## Information User instruction

## Safety gloves against chemical and mechanical risks

## Manufacturer

UVEX SAFETY Gloves GmbH & Co. KG Elso-Klöver-Str. 6, 21337 Lüneburg Postfach 24 47 · 21314 Lüneburg GERMANY

uvex rubiflex S - XG27B Type Basic glove material cotton interlock Available sizes 7, 8, 9, 10, 11

Tel.: +49 4131 9502-0 +49 4131 84338 Fax: gloves@uvex.de Email: Website: uvex-safety.de

**Coating material** 

Smallest packing unit


Special NBR (nitrile butadiene rubber) + XG grip coating 80 Pairs

**Pictogram and performance levels** EN 374 : 2003

EN 388 : 2003



Performance level



Pictogram and performance levels according to EN 374:2003 (lowest performance level: 1/highest performance: 6)

The sampling for penetration testing is made by general inspection level according to DIN 2859, part 1 with AQL 4.0.

Please note: The actual period of protection on the job is affected by many factors (temperature, abrasion, etc.) and can therefore differ from the performance level!

Pictogram and performance levels according to EN 388:2003 (highest performance level: 4/cut resistance: 5)

All levels only apply to the coated areas of the glove.

The noticeable difference in wearer comfort: combination of high sensitivity and tactile feel, lightness. The uvex phynomic airLite C ESD is certified according to the DIN EN 16350:2014 (1149-2) standard and is also tested based on the DIN EN 1149-1. Therefore it is perfectly applicable in ESD areas and

Warning	Gloves should not be worn where there is a risk of being caught in moving machinery parts.
Disposal	The gloves should be disposed of properly as household waste. If they come into contact with chemicals, please consult the chemical manufacturer's waste disposal guidelines.
	After contamination, a change of performance cannot be excluded. We are not aware of any substances in this product that could cause an allergic reaction.
Handling	Thoroughly check before use for damage. Defective gloves should not be used. All technical data refers to the state of the gloves at delivery, unused, not stretched and at ambient temperature (EN 374). Gloves must be disposed of when the permeation time expires.
Storage	Store in a dark, dry place.
Cleaning	Cleaning only possible when not working with aggressive chemicals. Carefully rinse gloves under lukewarm running water.
EC notified body	TÜV Rheinland LGA Products GmbH Tillystraße 2 · 90431 Nürnberg No.: 0197

## protecting people